# **TECHNICAL DATA SHEET**



# AS2500 2 part Industrial Adhesive Sealant

#### Description

This is a novel twin pack system, which consists of a 1-Part RTV Silicone Sealant and an accelerator in a 10:1 mix ratio. By extruding the system through a static mixer nozzle, the intimately mixed material behaves like a conventional silicone sealant, but has the advantage of very rapid cure - less than 3 hours to almost full cure, allowing for very fast assembly. The sealant will cure anaerobically (without atmospheric moisture) in approximately 2 hours which is not possible with a conventional 1-Part RTV sealant.

#### **Key Features**

- Very fast room temperature cure
- Good adhesion to most substrates
- Anaerobic cure
- Reduced odour

## Application

Applications include but not limited to, assembly, cooking hobs and glass for cooker doors, and automotive  $\mathsf{FIPG}$ 

#### **Use and Cure Information**

This product is supplied as a twin pack 10:1 system.

When supplied in bulk containers A & B parts should be mixed at a ratio of 10:1 by volume using an automated machine with a static mixer nozzle. IMPORTANT: Mixed material in the mixer nozzle will cure quickly, therefore a continuous application process will avoid wasted material. A mixer nozzle of at least 9 GXF type elements is recommended for uniform mixing of both components.

The product can also be supplied in a high-quality twin cartridge system, the A part in a 240ml cartridge and the B part in a 24ml integral cartridge. To facilitate removal of the protective, plug a metal removable disc is located above the locking nut. The action of unscrewing the locking nut removes the plug. The static mixer nozzle is placed on the outlet and locked into place using the locking nut. (13mm). The stepped outlet of the static mixer nozzle is normally cut back 2 or 3 steps before fitting the cartridge into the dispensing gun\*. The cartridge is then located in the gun and pressed to click into place.

The sealant is extruded by applying a steady pressure to the trigger. In the case of the manually operated dispenser, full depression of the trigger should be maintained for as long as possible before releasing and reapplying trigger pressure. Complete mixing of each component is achieved within the first 50-60% of the nozzle.

All substrate surfaces should be clean and free of grease, the mixed sealant should be applied to one surface and contact made immediately, any additional tooling should be carried out within the tack free time shown opposite. Full cure times will vary slightly depending on the joint dimensions.

\* Excellent dual cartridge dispensers both manual and pneumatic are available from Sulzer Mixpac (UK) Limited – Ref DM 200.

#### Health & Safety Health and Safety

Safety Data Sheets available on request.

#### Packaging

CHT Adhesives are available in a variety packaging including cartridges and bulk containers. Please contact our sales department for more information.

Revision Date	29 Apr 2021
Revision No	1
Download Date	26 Apr 2024

The content set out in the technical data sheet does not contain information upon which you should rely. It is provided for general information purposes only and does not constitute a product specification. You must obtain professional or specialist advice before taking any action based on the information provided in the technical data sheet.

CHT make reasonable efforts to ensure that information set out in the technical data sheet is complete, accurate, and up-to-date. CHT do not, however, make any representations, warranties or guarantees (whether express or implied) that information set out in the technical data sheet is complete, accurate, or up-to-date or that the product will be suitable for your requirements. You should carry out your own testing to determine the applicability of such information and whether the product will be suitable. CHT reserve the right to modify the technical data sheet at any time. The CHT technical service department is available to offer further information and advice and should it be needed to look at modifying current products or custom formulate a new one to meet your specific requirements. Please contact the technical service department.

CHT Germany GmbH: Postfach 12 80, 72002 Tübingen, Bismarckstraße 102, 72072 Tübingen, Germany

Telephone: 07071/154-0, Fax: 07071/154-290, Email: info@cht.com, Homepage: www.cht.com / www.cht-silicones.com

Property	Test Method	Value
Uncured Product		
Appearance		Thixotropic paste
Color A		Translucent
Color B		Black
Cure Profile		23+/-2°C and 50+/-5% humidity
Cure Through to 3 mm Depth		1.5 hr
Cure Type		Acetoxy
Extrusion Rate g/min		304 g/min
Mix Ratio By Weight		10:1
Rheology		Paste
Self Bonding		Yes
Tack Free Time / Skin Formation at 23°C/73°F		4 min

### Cured Product

7 days at 23+/-2°C and 50+/-5% humidity

· · · · · · · · · · · · · · · · · · ·	· · · · · · · · · · · · · · · · · · ·	
100% Modulus (N/mm2)		0.91 MPa / 132 psi
CTE Linear ppm/°C		292 ppm / °C
CTE Volumetric ppm/°C		876 ppm/°C
Color		Black
Density	BS ISO 2781	1.05 g/cm3
Elongation at Break	ISO 37	280 %
Hardness Shore A	ASTM D 2240-95	39
Linear Shrinkage (%)		1 %
Max Working Temp		250 °C / 482 °F
Min Working Temp		-65 °C / -85 °F
Tear Resistance (N/mm)	BS ISO 34-1	5.5 N/mm / 31 ppi
Tensile Strength	ISO 37	2.32 N/mm2 / 336 psi
Thermal Conductivity		0.2 W/mK
Youngs Modulus (N/mm2)		0.65 N/mm2 / 94 psi

# **Electrical Properties**

Dielectric Constant	ASTM D-150	3
Dielectric Strength (V/mil)		457 V/mil
Dielectric Strength kV/mm	ASTM D-149	18 kV/mm / 457 V/mil
Dissipation Factor	ASTM D-150	0.0025
Volume Resistivity (Ohms cm)	ASTM D-257	7.77E+15 ohms cm
Storage		
Max Storage Temperature		40 °C / 104 °F

12 mths

Max Storage Temperature Shelf Life